


| | |
|---------------|------------|
| Customer P/N: | R614 |
| 产品图号 : | MWH08026BK |

| Version time | Elucidation | Change date | Change |
|--------------|-------------|-------------|--------|
| A/1 | 301增加极性和年轮 | 2013/11/07 | 梁境华 |
| A/2 | 301更新网尾 | 2014/03/29 | 黄培文 |
| A/3 | 301更新字版 | 2015/06/29 | 黄培文 |
| A/4 | 添加装箱数 | 2015/06/30 | 黄培文 |
| A/5 | 更新301插头 | 2015/07/15 | 苏锐华 |



| | | | | |
|-----|--|-----------------|---------|------|
| 6 | 6.6mm接线端子,黄铜本色, splice (STS 635BS-0或替代品) *2 | DWJXDZ0002T-0 | 3 | EA |
| 5 | 美式内架 insert | JB301030010 | 1 | EA |
| 4 | 平头非极性插片 terminal | DA001002ST-1 | 2 | EA |
| 3 | □4.75圆管端子 terminal | DYG47507LT-1 | 1 | EA |
| 2 | 美式三插NEMA 5-15P (XR-301) COLOR:黑色black PVC 30P | BC1030PBK0012 | 0.02174 | Kg |
| 1 | SJT 18AWG/3C 105°C COLOR:黑色black 裁线长:L=2000mm. | CUSJT3018A00101 | 2 | M |
| NO. | DESCRIPTION | XIONGRUN PN | QTY | UNIT |

| | | | | | |
|-------------|----------------|----------|------------|---------|------------|
| DESCRIPTION | AC POWER CABLE | DRAW NO. | XR-0672194 | UNIT | M M |
| PARTS NO | | SCALE | NONE | DATE | 01/08/2012 |
| APPROVED | | CHECKED | | DRAWING | |