

## Simply communicative

### Gigaset A415



- Illuminated, black-and-white 1.8" display with good contrast
- Illuminated send and hands-free key (green LED) and dedicated illuminated message key (red LED)
- Perfect sound quality with selectable sound profiles



#### Convenience - phoning essentials

Direct dial	yes
Bluetooth* function   Mini-USB   Micro-USB	-   -
Dial by voice command	-
Automatic redial function in handset	-
Automatic dialing of operator prefix	yes
Last dialed ... numbers	20
Phonebook transfer: via DECT   via Bluetooth*   via LAN	yes   -   -
Phonebook   address book   entries	yes   -   100
Standby time   talk time	200h   18h
Room monitoring	-
Vibracall	-
Call blocking	-
Live recording of calls	-
Calendar	-
Date reminder function   alarm call	-   yes
Plug-and-play installation	yes
Range indoors   outdoors	50m   300m

<b>Display and menu features</b>	
Charging status displayed	yes
Call duration displayed	yes
Call charge displayed	-
Range displayed (handset to base station)	yes
Date displayed	yes
Time displayed	yes
List of last ... missed calls with time and date	20
Display of caller's number (CLIP)   picture (Picture CLIP)	yes   -
Easy-to-use text-based menu   jumbo fonts   icon-based	yes   yes   yes
... pixel, ... inch, ... colours and ... lines	33 x 32 mm   1.8   96 x 64 px   6
Display: illuminated   colour	yes   -
Display: numeric   alphanumeric   semigraphical   graphical	-   -   -   yes
Multilingual menu for up to ... languages	19
<b>ECO DECT</b>	
Up to 60% less power consumption	yes
Transmitting power at almost zero when handset docked	yes
Radiation-free ECO Mode Plus	yes
ECO Mode for reduction of transmitting power of base station by 80%	yes
<b>Keypad features</b>	
Navigation key	yes
Message indicator key	yes
Colour of illumination	amber
Illuminated keypad	yes
<b>Messaging functions</b>	
Up to ... characters SMS   Email	-   -
Email notification	-
<b>Others</b>	
Wall mountable	yes
Warranty	2 years
Batteries	2xAAA
<b>SAR Value</b>	
Gigaset Handsets	< 0.1 W/kg
<b>Security</b>	
Equipped with speech transmission encryption	yes
<b>Sound quality</b>	
Hands-free talking   convenient hands-free   advanced hands-free	-   yes   -
Headset connection   corded 2,5 mm   Bluetooth*	-   -   -
Adjustable handset volume	yes
Individual ringer melodies for VIP entries	-
HSP™ for brilliant sound quality	yes
HDSP™ ready handset	yes
Ringer melodies   polyphonic   real sounds   downloadable	20   -   -   -
<b>Technical data</b>	
Wall mountable	yes
Standards DECT   GAP	yes   yes
Dimensions handset (H x W x D in mm)	155 mm x 49 mm x 34 mm / 110 g
Dimensions base station (H x W x D in mm)	44 mm x 88 mm x 103 mm / 71 g
Dimensions charger (H x W x D in mm)	39 mm x 72 mm x 76 mm / 35 g
Available colours	Black / White