

## Data sheet | Item number: 258-5000

Thermal transfer printer; smartPRINTER; for complete control cabinet marking; 300 dpi

[www.wago.com/258-5000](http://www.wago.com/258-5000)



RoHS   
Compliant

[BOMcheck.net](http://BOMcheck.net)

### Item description

Includes:

- Power supply and power cable
- USB cable
- One roll of marking strips and WMB Inline markers each
- 2x roller
- 1x reel holder
- 1x ink ribbon
- smartSCRIPT marking software and driver

### Data

#### Technical Data

Printing method	Thermal transfer
Print head	Glass layer, spring-mounted
Print resolution	300 dpi
Print resolution	300 dpi (12 pixels/mm)

Print speed	max. 127 mm/s (WAGO recommends 50.8 mm/s)
Print width	47 mm
Print length (max.)	762 mm
See-through/reflective sensor	yes, centrally fixed
RAM memory	8 MB Flash, 16 MB SDRAM
Interfaces	USB, RS-232, ETHERNET 10/100 Mbps
Operating voltage	100 ... 240 VAC, 50 ... 60 Hz (automatic adjustment)
Safety approvals	CE (EMC)
Operation display	Color TFT LCD with navigation button
Surrounding air (storage) temperature	-20 ... 50 °C
Ink ribbon	Reel outside diameter: 40 mm; core inside diameter 0.5" (12.7 mm); max. length 110 m; max. width 58 mm
Included	external unwinder, power supply + cable, USB cable, 2 empty cardboard roller cores

### Mechanical data

Width	135 mm / 5.315 inch
Height	175 mm / 6.89 inch
Depth	245 mm / 9.646 inch
Weight	3840 g

### Commercial data

Country of origin	TW
GTIN	4050821520993
Customs Tariff No.	84433210000
Product Group	14 (Tools)



### Approvals / Certificates
















#### UL-Approvals
















Logo	Approval	Certificate name
	UL UL Multiple Listing UL LLC	E482462


















### Compatible products




















#### Marking accessories

	Item no.: 2009-110 Marking strips; on reel; not stretchable; plain; snap-on type	<a href="http://www.wago.com/2009-110">www.wago.com/2009-110</a>
	Item no.: 2009-113 WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113">www.wago.com/2009-113</a>

	<b>Item no.: 2009-113/000-002</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-002">www.wago.com/2009-113/000-002</a>
	<b>Item no.: 2009-113/000-005</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-005">www.wago.com/2009-113/000-005</a>
	<b>Item no.: 2009-113/000-006</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-006">www.wago.com/2009-113/000-006</a>
	<b>Item no.: 2009-113/000-007</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-007">www.wago.com/2009-113/000-007</a>
	<b>Item no.: 2009-113/000-012</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-012">www.wago.com/2009-113/000-012</a>
	<b>Item no.: 2009-113/000-017</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-017">www.wago.com/2009-113/000-017</a>
	<b>Item no.: 2009-113/000-023</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-023">www.wago.com/2009-113/000-023</a>
	<b>Item no.: 2009-113/000-024</b> WMB-Inline; for smartPRINTER; on reel; plain; snap-on type	<a href="http://www.wago.com/2009-113/000-024">www.wago.com/2009-113/000-024</a>
	<b>Item no.: 2009-114</b> WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	<a href="http://www.wago.com/2009-114">www.wago.com/2009-114</a>
	<b>Item no.: 2009-114/000-002</b> WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	<a href="http://www.wago.com/2009-114/000-002">www.wago.com/2009-114/000-002</a>
	<b>Item no.: 2009-114/000-005</b> WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	<a href="http://www.wago.com/2009-114/000-005">www.wago.com/2009-114/000-005</a>
	<b>Item no.: 2009-114/000-006</b> WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	<a href="http://www.wago.com/2009-114/000-006">www.wago.com/2009-114/000-006</a>
	<b>Item no.: 2009-114/000-007</b> WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	<a href="http://www.wago.com/2009-114/000-007">www.wago.com/2009-114/000-007</a>
	<b>Item no.: 2009-114/000-012</b> WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	<a href="http://www.wago.com/2009-114/000-012">www.wago.com/2009-114/000-012</a>
	<b>Item no.: 2009-114/000-023</b> WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type	<a href="http://www.wago.com/2009-114/000-023">www.wago.com/2009-114/000-023</a>

	<p><b>Item no.: 2009-114/000-024</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 4 - 4.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-114/000-024">www.wago.com/2009-114/000-024</a></p>
	<p><b>Item no.: 2009-115</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115">www.wago.com/2009-115</a></p>
	<p><b>Item no.: 2009-115/000-002</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-002">www.wago.com/2009-115/000-002</a></p>
	<p><b>Item no.: 2009-115/000-005</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-005">www.wago.com/2009-115/000-005</a></p>
	<p><b>Item no.: 2009-115/000-006</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-006">www.wago.com/2009-115/000-006</a></p>
	<p><b>Item no.: 2009-115/000-007</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-007">www.wago.com/2009-115/000-007</a></p>
	<p><b>Item no.: 2009-115/000-012</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-012">www.wago.com/2009-115/000-012</a></p>
	<p><b>Item no.: 2009-115/000-017</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-017">www.wago.com/2009-115/000-017</a></p>
	<p><b>Item no.: 2009-115/000-023</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-023">www.wago.com/2009-115/000-023</a></p>
	<p><b>Item no.: 2009-115/000-024</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-115/000-024">www.wago.com/2009-115/000-024</a></p>
	<p><b>Item no.: 2009-135</b>                      WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-135">www.wago.com/2009-135</a></p>
	<p><b>Item no.: 2009-145</b>                      Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-145">www.wago.com/2009-145</a></p>
	<p><b>Item no.: 2009-145/000-002</b>                      Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-145/000-002">www.wago.com/2009-145/000-002</a></p>
	<p><b>Item no.: 2009-145/000-005</b>                      Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-145/000-005">www.wago.com/2009-145/000-005</a></p>
	<p><b>Item no.: 2009-145/000-006</b>                      Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<p><a href="http://www.wago.com/2009-145/000-006">www.wago.com/2009-145/000-006</a></p>

	<p><b>Item no.: 2009-145/000-007</b> Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<a href="http://www.wago.com/2009-145/000-007">www.wago.com/2009-145/000-007</a>
	<p><b>Item no.: 2009-145/000-012</b> Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<a href="http://www.wago.com/2009-145/000-012">www.wago.com/2009-145/000-012</a>
	<p><b>Item no.: 2009-145/000-023</b> Mini-WSB Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<a href="http://www.wago.com/2009-145/000-023">www.wago.com/2009-145/000-023</a>
	<p><b>Item no.: 2009-145/000-024</b> Mini-WSB Inline; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<a href="http://www.wago.com/2009-145/000-024">www.wago.com/2009-145/000-024</a>
	<p><b>Item no.: 2009-515</b> WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<a href="http://www.wago.com/2009-515">www.wago.com/2009-515</a>
	<p><b>Item no.: 2009-615</b> WMB-Inline; for smartPRINTER; on reel; stretchable 5 - 5.2 mm; plain; snap-on type</p>	<a href="http://www.wago.com/2009-615">www.wago.com/2009-615</a>
	<p><b>Item no.: 210-702</b> Marking strips; for smartPRINTER</p>	<a href="http://www.wago.com/210-702">www.wago.com/210-702</a>
	<p><b>Item no.: 210-801</b> Type labels</p>	<a href="http://www.wago.com/210-801">www.wago.com/210-801</a>
	<p><b>Item no.: 210-802</b> Type labels</p>	<a href="http://www.wago.com/210-802">www.wago.com/210-802</a>
	<p><b>Item no.: 210-803</b> Type labels</p>	<a href="http://www.wago.com/210-803">www.wago.com/210-803</a>
	<p><b>Item no.: 210-804</b> Type labels</p>	<a href="http://www.wago.com/210-804">www.wago.com/210-804</a>
	<p><b>Item no.: 210-805</b> Labels; for smartPRINTER</p>	<a href="http://www.wago.com/210-805">www.wago.com/210-805</a>
	<p><b>Item no.: 210-805/000-002</b> Labels; for smartPRINTER</p>	<a href="http://www.wago.com/210-805/000-002">www.wago.com/210-805/000-002</a>
	<p><b>Item no.: 210-806</b> Labels; for smartPRINTER</p>	<a href="http://www.wago.com/210-806">www.wago.com/210-806</a>
	<p><b>Item no.: 210-806/000-002</b> Labels; for smartPRINTER</p>	<a href="http://www.wago.com/210-806/000-002">www.wago.com/210-806/000-002</a>
	<p><b>Item no.: 210-807</b> Labels; for smartPRINTER</p>	<a href="http://www.wago.com/210-807">www.wago.com/210-807</a>
	<p><b>Item no.: 210-807/000-002</b> Labels; for smartPRINTER</p>	<a href="http://www.wago.com/210-807/000-002">www.wago.com/210-807/000-002</a>

	<b>Item no.: 210-808</b> Labels; for smartPRINTER	<a href="http://www.wago.com/210-808">www.wago.com/210-808</a>
	<b>Item no.: 210-810</b> Labels; for smartPRINTER	<a href="http://www.wago.com/210-810">www.wago.com/210-810</a>
	<b>Item no.: 210-811</b> Textile labels; for smartPRINTER	<a href="http://www.wago.com/210-811">www.wago.com/210-811</a>
	<b>Item no.: 210-811/000-002</b> Textile labels; for smartPRINTER	<a href="http://www.wago.com/210-811/000-002">www.wago.com/210-811/000-002</a>
	<b>Item no.: 210-812</b> Type labels	<a href="http://www.wago.com/210-812">www.wago.com/210-812</a>
	<b>Item no.: 210-813</b> Labels; for smartPRINTER	<a href="http://www.wago.com/210-813">www.wago.com/210-813</a>
	<b>Item no.: 210-831</b> Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive	<a href="http://www.wago.com/210-831">www.wago.com/210-831</a>
	<b>Item no.: 210-832</b> Marking strips; on reel; 3 mm wide; plain; Self-adhesive	<a href="http://www.wago.com/210-832">www.wago.com/210-832</a>
	<b>Item no.: 210-833</b> Marking strips; on reel; 6 mm wide; plain; Self-adhesive	<a href="http://www.wago.com/210-833">www.wago.com/210-833</a>
	<b>Item no.: 210-834</b> Marking strips; on reel; 5 mm wide; plain; Self-adhesive	<a href="http://www.wago.com/210-834">www.wago.com/210-834</a>
	<b>Item no.: 210-847</b> Push-button marker	<a href="http://www.wago.com/210-847">www.wago.com/210-847</a>
	<b>Item no.: 210-848</b> Push-button marker	<a href="http://www.wago.com/210-848">www.wago.com/210-848</a>
	<b>Item no.: 210-850</b> Push-button marker	<a href="http://www.wago.com/210-850">www.wago.com/210-850</a>
	<b>Item no.: 210-852</b> Push-button marker	<a href="http://www.wago.com/210-852">www.wago.com/210-852</a>
	<b>Item no.: 210-854</b> Push-button marker	<a href="http://www.wago.com/210-854">www.wago.com/210-854</a>
	<b>Item no.: 210-855</b> Push-button marker	<a href="http://www.wago.com/210-855">www.wago.com/210-855</a>
	<b>Item no.: 210-856</b> Push-button marker	<a href="http://www.wago.com/210-856">www.wago.com/210-856</a>
	<b>Item no.: 210-858</b> Push-button marker	<a href="http://www.wago.com/210-858">www.wago.com/210-858</a>
	<b>Item no.: 210-860</b> Push-button marker	<a href="http://www.wago.com/210-860">www.wago.com/210-860</a>
	<b>Item no.: 210-862</b> Push-button marker	<a href="http://www.wago.com/210-862">www.wago.com/210-862</a>



**Item no.: 210-870**  
Marking strips; for smartPRINTER

[www.wago.com/210-870](http://www.wago.com/210-870)



**Item no.: 210-871**  
Marking strips; for smartPRINTER

[www.wago.com/210-871](http://www.wago.com/210-871)



**Item no.: 210-872**  
Marking strips; for smartPRINTER

[www.wago.com/210-872](http://www.wago.com/210-872)



**Item no.: 210-873**  
Marking strips; for smartPRINTER

[www.wago.com/210-873](http://www.wago.com/210-873)



**Item no.: 210-874**  
Marking strips; for smartPRINTER

[www.wago.com/210-874](http://www.wago.com/210-874)



**Item no.: 210-875**  
Marking strips; for smartPRINTER

[www.wago.com/210-875](http://www.wago.com/210-875)



**Item no.: 210-876**  
Marking strips; for smartPRINTER

[www.wago.com/210-876](http://www.wago.com/210-876)



**Item no.: 210-876/000-002**  
Marking strips; for smartPRINTER

[www.wago.com/210-876/000-002](http://www.wago.com/210-876/000-002)



**Item no.: 210-877**  
Marking strips; for smartPRINTER

[www.wago.com/210-877](http://www.wago.com/210-877)



**Item no.: 211-500**  
Shrink tube; for smartPRINTER

[www.wago.com/211-500](http://www.wago.com/211-500)



**Item no.: 211-500/000-002**  
Shrink tube; for smartPRINTER

[www.wago.com/211-500/000-002](http://www.wago.com/211-500/000-002)



**Item no.: 211-501**  
Shrink tube; for smartPRINTER

[www.wago.com/211-501](http://www.wago.com/211-501)



**Item no.: 211-501/000-002**  
Shrink tube; for smartPRINTER

[www.wago.com/211-501/000-002](http://www.wago.com/211-501/000-002)



**Item no.: 211-502**  
Shrink tube; for smartPRINTER

[www.wago.com/211-502](http://www.wago.com/211-502)



**Item no.: 211-502/000-002**  
Shrink tube; for smartPRINTER

[www.wago.com/211-502/000-002](http://www.wago.com/211-502/000-002)





















**Item no.: 211-503**  
Shrink tube; for smartPRINTER

[www.wago.com/211-503](http://www.wago.com/211-503)












**Item no.: 211-503/000-002**  
Shrink tube; for smartPRINTER

[www.wago.com/211-503/000-002](http://www.wago.com/211-503/000-002)

	<b>Item no.: 211-504</b> Shrink tube; for smartPRINTER	<a href="http://www.wago.com/211-504">www.wago.com/211-504</a>
	<b>Item no.: 211-504/000-002</b> Shrink tube; for smartPRINTER	<a href="http://www.wago.com/211-504/000-002">www.wago.com/211-504/000-002</a>
	<b>Item no.: 211-505</b> Shrink tube; for smartPRINTER	<a href="http://www.wago.com/211-505">www.wago.com/211-505</a>
	<b>Item no.: 211-505/000-002</b> Shrink tube; for smartPRINTER	<a href="http://www.wago.com/211-505/000-002">www.wago.com/211-505/000-002</a>
	<b>Item no.: 211-506</b> Shrink tube; for smartPRINTER	<a href="http://www.wago.com/211-506">www.wago.com/211-506</a>
	<b>Item no.: 211-506/000-002</b> Shrink tube; for smartPRINTER	<a href="http://www.wago.com/211-506/000-002">www.wago.com/211-506/000-002</a>
	<b>Item no.: 211-811</b> Marker card; for smartPRINTER; for use in nozzles	<a href="http://www.wago.com/211-811">www.wago.com/211-811</a>
	<b>Item no.: 211-821</b> Marker card; for smartPRINTER; for use in nozzles	<a href="http://www.wago.com/211-821">www.wago.com/211-821</a>
	<b>Item no.: 211-835</b> Cable tie marker; for smartPRINTER; for use with cable ties	<a href="http://www.wago.com/211-835">www.wago.com/211-835</a>
	<b>Item no.: 211-836</b> Cable tie marker; for smartPRINTER; for use with cable ties	<a href="http://www.wago.com/211-836">www.wago.com/211-836</a>
	<b>Item no.: 211-836/000-002</b> Cable tie marker; for smartPRINTER; for use with cable ties	<a href="http://www.wago.com/211-836/000-002">www.wago.com/211-836/000-002</a>
	<b>Item no.: 211-855</b> Self-laminating labels; for smartPRINTER	<a href="http://www.wago.com/211-855">www.wago.com/211-855</a>
	<b>Item no.: 211-856</b> Self-laminating labels; for smartPRINTER	<a href="http://www.wago.com/211-856">www.wago.com/211-856</a>
	<b>Item no.: 211-857</b> Self-laminating labels; for smartPRINTER	<a href="http://www.wago.com/211-857">www.wago.com/211-857</a>
	<b>Item no.: 211-861</b> Conductor markers for thread-on mounting; for smartPRINTER	<a href="http://www.wago.com/211-861">www.wago.com/211-861</a>
	<b>Item no.: 211-862</b> Conductor markers for thread-on mounting; for smartPRINTER	<a href="http://www.wago.com/211-862">www.wago.com/211-862</a>
	<b>Item no.: 211-863</b> Conductor markers for thread-on mounting; for smartPRINTER	<a href="http://www.wago.com/211-863">www.wago.com/211-863</a>
	<b>Item no.: 258-5005</b> Thermal transfer ink ribbon; for smartPRINTER; 48 mm wide	<a href="http://www.wago.com/258-5005">www.wago.com/258-5005</a>
	<b>Item no.: 258-5006</b>	



	Roller; for smartPRINTER; for marking strips, device and equipment markers, conductor and cable markers	<a href="http://www.wago.com/258-5006">www.wago.com/258-5006</a>
	<b>Item no.: 258-5007</b> Roller; for smartPRINTER; for WMB-Inline WAGO (2009-115, -114, -113); 1 grinding device	<a href="http://www.wago.com/258-5007">www.wago.com/258-5007</a>
	<b>Item no.: 258-5008</b> Roller; for smartPRINTER; for Mini-WSB Inline WAGO (2009-145); 1 grinding device	<a href="http://www.wago.com/258-5008">www.wago.com/258-5008</a>
	<b>Item no.: 258-5009</b> Roller; for smartPRINTER; for WMB-Inline Phoenix (2009-515); 1 grinding device	<a href="http://www.wago.com/258-5009">www.wago.com/258-5009</a>
	<b>Item no.: 258-5010</b> Roller; for smartPRINTER; for WMB-Inline Weidmüller (2009-615); 1 grinding device	<a href="http://www.wago.com/258-5010">www.wago.com/258-5010</a>
	<b>Item no.: 258-5014</b> Thermal transfer ink ribbon; for smartPRINTER; 48 mm wide; for self-laminating labels	<a href="http://www.wago.com/258-5014">www.wago.com/258-5014</a>
	<b>Item no.: 258-5015</b> Presentation- and transport case for smartPRINTER	<a href="http://www.wago.com/258-5015">www.wago.com/258-5015</a>
	<b>Item no.: 258-5030</b> Cutter; for smartPRINTER; for marking strips, equipment markers, conductor and cable markers; Durable; High accuracy	<a href="http://www.wago.com/258-5030">www.wago.com/258-5030</a>
	<b>Item no.: 709-178</b> Marking strips; on reel; 7.5 mm wide; not stretchable; plain; snap-on type	<a href="http://www.wago.com/709-178">www.wago.com/709-178</a>

## Downloads

### Documentation

#### Additional Information

smartPRINTER Poster, installation guide, quick start	Apr 16, 2018	5.8 MB	Download
smartPRINTER handling instructions, cutting notice	Apr 16, 2018	2.1 MB	Download
smartPRINTER operating instructions	Apr 16, 2018	3.2 MB	Download
smartPRINTER handling instructions, allocation roller printing material	Apr 16, 2018	162.5 kB	Download
smartPRINTER cutter instructions	Apr 16, 2018	578.2 kB	Download
smartPRINTER FAQ fault description and troubleshooting	Apr 16, 2018	83.9 kB	Download
smartPRINTER handling instructions, accessories	Apr 16, 2018	873.7 kB	Download



smartPRINTER handling instructions, IT infrastructure requirements	Apr 16, 2018	36.6 kB	Download
--	--------------	---------	----------

smartPRINTER instructions external unwinder	Apr 16, 2018	1.0 MB	Download
---	--------------	--------	----------

## Application Notes

### Application Note CoDeSys 2.3

Replacement of media feed	Jul 10, 2015	PDF 2.3 MB	Download
---------------------------	--------------	---------------	----------

## Engineering-Software

### Configuration and Commissioning Software

WAGO Printer Settings	2.4.3.3 Apr 12, 2018	ZIP 6.9 MB	Download
-----------------------	-------------------------	---------------	----------

WAGO smartPRINTER installation package	1.1.1.0 Apr 12, 2018	ZIP 67.8 MB	Download
--	-------------------------	----------------	----------

## smartDATA

### Desktop Application

WAGO smartLABEL	2.2 Apr 12, 2018	ZIP 31.5 MB	Download
-----------------	---------------------	----------------	----------

WAGO smartSCRIPT	3.88.15.1 Apr 12, 2018	ZIP 37.1 MB	Download
------------------	---------------------------	----------------	----------

WAGO GoDoctor	1.001 Apr 12, 2018	ZIP 810.4 kB	Download
---------------	-----------------------	-----------------	----------

### Firmware and driver

WAGO smartPRINTER Firmware Required for use of 2009-615 for WMB Inline Weidmüller	V1.UW7q Apr 12, 2018	ZIP 2.2 MB	Download
--	-------------------------	---------------	----------

## Device Files

### Device Driver

WAGO smartPRINTER Driver	7.4.2 Apr 18, 2018	ZIP 14.3 MB	Download
--------------------------	-----------------------	----------------	----------



Subject to changes.

---

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.