

## Parallel screw clamp PA

### Product characteristics

Spindle of steel, browned

Clamping jaws of steel, zinc coated



### Technical data

Article	Opening A [mm]	Throat depth B [mm]	Jaw length C [mm]	Jaw height D [mm]	Cross section E [mm]	Thread [mm]	Weight [kg]
PA28	36	19	52	6	9,6 x 9,6	M5 x 0,8	0,08
PA40	46	26	64	7,2	12,8 x 12,8	M6 x 1	0,10
PA55	60	35	79	7,2	12,8 x 12,8	M6 x 1	0,18
PA70	87	50	106	7	16 x 16	M8 x 1,25	0,43
PA105	116	72	155	5,2	19 x 19	M8 x 1,26	0,92

