

2.5" MOBILE RACK SERIES

1 x 2.5" SATA /SAS HDD or SSD

2.5" to 3.5 HDD Size Adapter

Support SAS 12G
Trayless Design

ST-1111SS



Form Factor	1 X 3.5" HDD Size
SSD Type	1 X 2.5" SATA / SAS HDD/ SSD
Transfer Rate	SATA I, II, III & SAS I, II, III (12Gbps)
Interface	7pin SATA Connector X 1 15pin SATA Power Connector X 1
Material	All Plastic Trayless Body Design
LED	Power On- Blue; HDD Access- Purple Blinking
Dimension	146.0(L) X 101.5(W) X 25.0(H) mm



Support upto 12Gbps Performance

Support upto the highest 12Gbps transmission performance and downward support 6Gbp



Test Speed		(Test Result)
SAS 3.0	Read	1338MB/S
	Write	1124MB/S
(Theoretical Speed)		
SAS 2.0	Read	600MB/S
	Write	600MB/S



2.5" to 3.5" Adapter Cage

- *3.5" form factor for 1 x 2.5" HDD/SSD
- *Fit 1 x 2.5" SSD/HDD into a 3.5" form factor size space

Trayless Body with Actuator Guiding Design

All plastic body and trayless bezel with Patent actuator guiding design, pull out the SSD/HDD in a second.



LED Indication Design

Blue: Power ON

Purple Blinking: HDD Accessing

2.5" MOBILE RACK SERIES

1 x 2.5" SATA /SAS HDD or SSD

ST-111SS



Form Factor 1 X 3.5" HDD Size

Support HDD Type 1 X 2.5" SATA I, II, III & SAS I, II, III (12Gbps) HDD/ SSD

Interface 7pin SATA Connector X 1
15pin SATA Power Connector X 1

LED Indication Power On- Blue
HDD Access- Purple Blinking

Security Design Mechanical Sliding Lock

Material Plastic

Fan N/A

Accessories  Screws For Mounting SATA SSD(IT3*6mm Φ8mm) X 4pcs
 Screws For Mounting On Chassis(TM3*5mm) X 6pcs

Operating System Windows/ Linux/Mac

Product Dimension 146.0(L) X 101.5(W) X 25.0(H) Mm

Product Weight 0.14kg