

Keyword:
Enhanced Start



Type: **SL-760**

Performance Data **Size AA**
 (Typical values for batteries stored at 25°C for one year)


| | |
|-----------------------------------|----------------------|
| System | Li/SOCl ₂ |
| Nominal voltage | 3.6 V |
| Nominal capacity | 2.1 Ah |
| Nominal current | 2 mA |
| Max. continuous discharge current | 60 mA |
| Pulse current capability | 140 mA |
| Anode surface area | 14 cm ² |
| Weight | 18 g |
| Volume | 8.0 cm ³ |
| Temperature range | -55...+85 °C |

WARNING:
 Fire, explosion, and severe burn hazard. Do not recharge, disassemble, heat above 100 °C, incinerate, or expose contents to water.


Typical Discharge Curves at +25°C




Available Capacity



Operating Voltage



Pulse Discharge Characteristics at +25°C



Available Terminations

| | |
|-----------|----------------|
| SL-760/S | Standard |
| SL-760/T | Tags |
| SL-760/P | Pins |
| SL-760/PR | Pins Radial |
| SL-760/PT | Polarized Tags |

Catalogue No.

| |
|---------------|
| 11 1 07601 00 |
| 11 1 07602 00 |
| 11 1 07603 00 |
| 11 1 07606 00 |
| 11 1 07608 00 |

Any values given here are for information purposes only. They also depend on actual conditions of use and are not warranties of future performance. Subject to change.