

PRODUCT DATASHEET



Product	AGFAPHOTO Alkaline Battery
Type/Size	Micro AAA LR03



An Gut Nazareth 18 a
52353 Düren, Germany
Tel. +49(0)2421/20856-0
Fax +49(0)2421/20856-29
service@german-battery.de
www.german-battery.de

Specifications

Chemical system	zinc-manganese-dioxide (free of mercury and cadmium)	
Dimensions	Diameter:	9.5 - 10.5 mm
	Height:	43.3 - 44.5 mm
Weight (approx.)	11,8 g	
Packaging	4 batteries in blister-pack with punch hole	
Nominal voltage	1.5 V	
Operating Temp:	18°C-55°C	
Capacity	1,150 mAh (75 Ω , 24 h/d, 0.9 V)	

Example discharge times / service life on different applications

Load resistance	20 Ω	24 Ω	5.1 Ω	10 Ω	75 Ω	600 mA
Daily period	24 h/d	15 s/min, 8 h/d	4 min/h, 8 h/d	1 h/d	4 h/d	10 s/min, 1 h/d
Cut-off voltage	0.9 V	1.0 V	0.9 V	0.9 V	0.9 V	0.9 V
Initial	≥ 18 hrs.	≥ 19 hrs.	≥ 225 min.	≥ 480 min.	≥ 70 hrs.	≥ 280 times
After 12 months of storage	≥ 17.2 hrs.	≥ 18 hrs.	≥ 210 min.	≥ 450 min.	≥ 65 hrs.	≥ 250 times
Application	-	control	torch	tape recorder	radio	camera flash light

Typical discharge characteristics

