

PRODUCT DATASHEET

GBT

Product	AGFAPHOTO Alkaline Battery
Type/Size	Mignon AA LR6



An Gut Nazareth 18 a
52353 Düren, Germany
Tel. +49(0)2421/20856-0
Fax +49(0)2421/20856-29
service@german-battery.de
www.german-battery.de

Specifications

Chemical system	zinc-manganese-dioxide (free of mercury and cadmium)	
Dimensions	Diameter:	13.5 - 14.5 mm
	Height:	49.2 - 50.5 mm
Weight (approx.)	24 g	
Packaging	4 batteries in blister-pack with punch hole	
Nominal voltage	1.5 V	
Operating Temp:	18°C-55°C	
Capacity	2,600 mAh (43 Ω, 24 h/d, 0.9 V)	

Example discharge times / service life on different applications

Load resistance	10 Ω	24 Ω	3.9 Ω	10 Ω	43 Ω	1.000 mA
Daily period	24 h/d	pulse	1 h/d	1 h/d	1 h/d	10 s/min, 1 h/d
Cut-off voltage	0.9 V	1.0 V	0.8 V	0.9 V	0.9 V	0.9 V
Initial	≥ 19 hrs.	≥ 43 hrs.	≥ 7 hrs.	≥ 19 hrs.	≥ 90 hrs.	≥ 350 times
After 12 months of storage	≥ 18 hrs.	≥ 40 hrs.	≥ 6,5 hrs.	≥ 18 hrs.	≥ 85 hrs.	≥ 320 times
Application	-	control	motor, toy	tape recorder	radio	camera flash light

Typical discharge characteristics

