

PRODUCT DATASHEET

Product	AGFAPHOTO Alkaline Battery
Type/Size	Baby C LR14



GBT

An Gut Nazareth 18 a
52353 Düren, Germany
Tel. +49(0)2421/20856-0
Fax +49(0)2421/20856-29
service@german-battery.de
www.german-battery.de

Specifications

Chemical system	zinc-manganese-dioxide (free of mercury and cadmium)
Dimensions	Diameter: 24.9 - 26.2 mm
	Height: 48.6 - 50.0 mm
Weight (approx.)	75 g
Packaging	2 batteries in blister-pack with punch hole
Nominal voltage	1.5 V
Operating Temp:	18°C-55°C
Capacity	6,200 mAh (6.8 Ω, 24 h/d, 0.9 V)

Example discharge times / Service life

Load resistance	3.9 Ω	3.9 Ω	3.9 Ω	6.8 Ω	20 Ω
Discharge mode	24 h/d	4 min/h, 8 h/d	1 h/d	1 h/d	4 h/d
Endvoltage	0.9 V	0.9 V	0.8 V	0.9 V	0.9 V
Initial	18 hrs.	18 hrs.	19 hrs.	34 hrs.	110 hrs.
After 12 months of storage	17 hrs.	17 hrs.	17.5 hrs.	31 hrs.	105 hrs.

Typical discharge characteristics

