
## Zinc Air Battery

## **A10**

# Z



#### **SPECIFICATIONS:**

Nominal Voltage: 1.4V
Rated Capacity: 90mAh

at  $3000\Omega$ 

to 0.9V

at 25℃ RH 60%

Average weight 0.31g

<u>Volume: 0.08cm<sup>3</sup></u>

Terminals: FLAT

Operating Temp.  $0^{\circ}$ C to Range:  $50^{\circ}$ C

Impedance:  $\leq 8\Omega$ 


at AC 1000Hz

Limiting current: 3mA

@1.1V

IEC: PR70

### DISCHARGE CHARACTERISTICS AT 3KΩ 25°C RH 60%



**Z** B, Z E H T

This data sheet is subject to change without prior notice. Contact us for the latest information. Contents here do not constitute a warranty.

July, 2007