

ENERGIZER A23

ZEROMERCURY®


Miniature Alkaline



Specifications

Classification:	Miniature Alkaline
Chemical System:	Manganese Dioxide (MnO ₂)
Designation:	ANSI-1181A
Nominal Voltage:	12 volts
Typical Capacity:	50 mAh to 6.0 Volts (rated at 20K ohms at 21°C)
Typical Weight:	8.0 grams (0.3 oz.)
Typical Volume:	1.1 cubic centimeters (0.07 cubic inch)
Jacket:	Metal
Terminal:	Flat Contact


Industry Standard Dimensions



**Designed for electronic applications
which may require high rate pulses.**

Milliamp-Hours Capacity

Continuous discharge to 6.0 volts at 21°C




Typical Discharge Durations

Continuous discharge at 21°C

Schedule (time)	Drain (mA)	Load (ohms)	Cutoff Voltage		
			8.8V (hours)	7.2V (hours)	6.0V (hours)
Continuous	0.5	20K	92	98	100

Discharge Characteristics

Schedule: Continuous
Typical Load: 20 KΩ (21°C)



Important Notice

This data sheet contains typical information specific to products manufactured at the time of its publication.
Contents herein do not constitute a warranty and are for reference only.