




Date	SYM	REVISION RECORD	AUTH	DR.	CK.
4/14/07	A	ADDED "ROHS COMPLIANT" UPDATED MATERIAL SPEC.	T.B.	B.S.	
5/05/07	B	UPDATED TOLERANCE AND TITLE BLOCK	T.B.	B.S.	
8/06/14	C	UPDATED TO ROHS 2 COMPLIANT	T.B.	B.S.	



## SPECIFICATIONS

Plastic material - Polypropylene, PP-1040  
 Flammability Rating -UL94-HB, UL File NO. E216959  
 Temperature Range: -10°C to +100°C  
 Springs - Nickel Plated Spring Steel  
 Rivets - Brass, Nickel Plated  
 9Volt Snaps - Brass, Nickel Plated  
 Contact Resistance: Under 50mΩ for +/- contacts per EIA-540J000  
 ROHS 2 COMPLIANT

Tolerance (Except as noted)			
decimal ±.5 (.020)		Scale 1=1	Drawn By T.S.
Fractional ± .8 (.030)	Title FOUR "C" CELL HOLDER WITH SOLDER LUGS		
Angular ± 3°	Date 8/06/14	Drawing Number BH22CL	
		Approved By T.B.	