


Data Sheet



Type Number 6237
Designation IEC ---
System Li-Manganese dioxide / Organic Electrolyte

UL Recognition:..... MH 13654 (N)
Nominal Voltage 3 V
Typical Capacity C 1350 mAh
 Load 1.0 kOhm, at 20°C down to 2.0 V

Weight (approx.) 15 g
Volume 5,6 ccm
Coding..... Date of Manufacturing Quarter / Year

Temperature Ranges

	min	max.
Storage	-55°C	75 °C
Discharge	-30°C	75°C

Dimensions

	min	max.
Diameter (A)	14,45	14,75
Height (B)	33,1	33,5
Shoulder Diameter[L].....	7	
Shoulder Height [M].....	0,6	

Segment Electronic

Main Applications Electronic

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0 V
Continuous 24h/d,7d/w	1000 Ω	Time:	500 h
		Capacity [mAh]:	1350
		Energy [MWh]:	3600