



Type Designation	6103
System	Lithium / Iron Disulfide (Li/FeS ₂)
Shelf Life (Coding)*	15 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	1100
Permissible Temperature Range	- 40 °C ... 60 °C
Weight, approx. [g]	7,3

Dimensions [mm]	min:	max:
∅	9.5	10.5
A	-	44.5
B	43.5	-
F	-	3.8
G	0.8	-

Typical Capacities (at 20°C):



Discharge Type	Load	End Voltage[V]	1.05
2S/28S, 5M/H Digital Still Camera	1200/650 mA	Pulse [n]	114
Discharge Type	Load	End Voltage[V]	0.9
10S/M, 1H/D, 7D/W Photo Flash	600 mA	Pulse [n]	605

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

* In consideration of typical loss of capacity at storage and application.