



Type Number..... 6016
Designation IEC..... CR 2016
System..... Li-Manganese dioxide/
 Organic Electrolyte

UL Recognition..... MH 13654
Nominal Voltage..... 3 V
Typical Capacity C..... 87 mAh

Temperature Ranges min max.
 Storage..... -55°C 70°C
 Discharge..... -20°C 70°C

Dimensions min max.
 Diameter (A) 19,7 20,0
 Height (B)..... 1,4 1,6
 Shoulder Diameter [E] 18,4
 Shoulder Height [C] 0,1

Weight (approx.)..... 1,8 g

Typical Capacities (at 20°C)

Discharge Type	Load	End Voltage:	2.0V
Continuous 24h/d, 7d/w	30000 Ω	Time: [h]:	930

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries.

All Data contained herein is for single cells

For battery applications, performance data may vary from single cell data, depending on specific battery configuration