

# Data Sheet

Recommended Application: **Universal**

**Industrial**

**4003**

**Conrad:651203**

Type Designation	4003
Designation IEC	LR03
System	Zn-MnO <sub>2</sub> (Alkaline)
Shelf Life (Coding)*	5 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	1220 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	11
Volume [ccm]	3.5

## Dimensions [mm]

min: max:

Ø	9.5	10.5
A	-	44.5
B	43.5	-
C	4.3	-
E	-	0.5
F	-	3.8
G	0.8	-

