

# Data Sheet

Recommended Application: **Universal**

**Industrial**

**4006**

**Conrad:651206**

Type Designation	4006
Designation IEC	LR6
System	Zn-MnO <sub>2</sub> (Alkaline)
Shelf Life (Coding)*	5 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	2900 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	24
Volume [ccm]	7.62

## Dimensions [mm]

min: max:

Ø	13.5	14.5
A	-	50.5
B	49.5	-
C	7.0	-
E	-	0.5
F	-	5.5
G	1.0	-

