



## Data

### Electrical data

#### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
Rated impulse voltage (III / 3)	8 kV

### Geometrical Data

Width	23.9 mm / 0.941 inch
Height	19 mm / 0.748 inch
Depth	4.1 mm / 0.161 inch

### Material Data

Color	light gray
Fire load	0.018 MJ
Weight	2.04 g



## Commercial data

Country of origin	DE
GTIN	4045454945633
Customs Tariff No.	85366990990

## Downloads

### Documentation

#### Bid Text

2001-406/020-000	Oct 20, 2017	DOC 24.1 kB	Download
------------------	--------------	----------------	----------

## smartDATA

### CAD data

3D Download 2001-406/020-000	URL	Download
------------------------------	-----	----------

## Product family

### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.