



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color:

## Data

### Electrical data

Rated current (Ex e II)	50 A
-------------------------	------

### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	57 A
---------------	------

### Geometrical Data

Width	37.6 mm / 1.48 inch
-------	---------------------

Height	23 mm / 0.906 inch
--------	--------------------

Depth	4.1 mm / 0.161 inch
-------	---------------------



## Material Data

Color	light gray
Fire load	0.029 MJ
Weight	6.15 g

## Commercial data

Country of origin	DE
GTIN	4044918578691
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

## Downloads

### Documentation

#### Bid Text

2010-434	Oct 26, 2017	DOC 24.1 kB	Download
----------	--------------	----------------	----------

## smartDATA

### CAD data

3D Download 2010-434	URL	Download
----------------------	-----	----------

## Product family

### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.