



RoHS Compliant

BOMcheck.net

Color:

Data

Electrical data

Rated current (Ex e II)	65 A
-------------------------	------

Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	76 A
---------------	------

Geometrical Data

Width	57.5 mm / 2.264 inch
-------	----------------------

Height	23 mm / 0.906 inch
--------	--------------------

Depth	4.1 mm / 0.161 inch
-------	---------------------



Material Data

Color	light gray
Fire load	0.042 MJ
Weight	9.34 g

Commercial data

Packaging type	bag
Country of origin	DE
GTIN	4055143702447
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

Downloads

Documentation

Bid Text

2016-435	Oct 26, 2017	DOC 24.1 kB	Download
----------	--------------	----------------	----------

smartDATA

CAD data

3D Download 2016-435	URL	Download
----------------------	-----	----------

Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.