

Data

Electrical data

Approvals per UL 1059

Rated voltage UL (Use Group B)	300 V
Rated current UL (Use Group B)	20 A
Rated voltage UL (Use Group C)	300 V
Rated current UL (Use Group C)	20 A
Rated voltage UL (Use Group D)	600 V
Rated current UL (Use Group D)	5 A

Geometrical Data

Width	0.8 mm / 0.031 inch
Height	51.7 mm / 2.035 inch
Depth	69.7 mm / 2.744 inch



Material Data


Color	gray
Fire load	0.072 MJ
Weight	2.41 g

Commercial data

Country of origin	CN
GTIN	4044918691161
Customs Tariff No.	85389099990
Product Group	22 (TOPJOB S)

Approvals / Certificates

Ex-Approvals

Logo	Approval	Certificate name
	IECEX Physikalisch Technische Bundesanstalt	IECEX PTB 03.0004U

Downloads

Documentation

Bid Text

2002-2291	Oct 25, 2017	DOC 24.1 kB	Download
-----------	--------------	----------------	----------

smartDATA

CAD data

3D Download 2002-2291	URL	Download
-----------------------	-----	----------



Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.