



RoHS  
Compliant ✓

BOMcheck.net

Color: ■

## Data

### Electrical data

Rated current (Ex e II)	20 A
-------------------------	------

### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	25 A
---------------	------

### Geometrical Data

Width	29.5 mm / 1.161 inch
-------	----------------------

Height	19 mm / 0.748 inch
--------	--------------------

Depth	4.1 mm / 0.161 inch
-------	---------------------

### Material Data

Color	blue
-------	------

Fire load	0.021 MJ
-----------	----------



Weight	2.916 g
--------	---------

---

### Commercial data

Country of origin	DE
GTIN	4050821077770
Customs Tariff No.	85366990990

---

### Downloads

#### Documentation

#### Bid Text

2002-406/000-006	Oct 20, 2017	DOC 24.6 kB	Download
------------------	--------------	----------------	----------

---

### smartDATA

#### CAD data

3D Download 2002-406/000-006	URL	Download
------------------------------	-----	----------

---

### Product family

#### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.