



Data

Electrical data

Rated current (Ex e II) 20 A

Ratings per IEC/EN 60664-1

Rated voltage (III / 3) 800 V

Rated current 25 A



## Geometrical Data

Width	19.1 mm / 0.752 inch
Height	19 mm / 0.748 inch
Depth	4.1 mm / 0.161 inch

## Material Data

Color	light gray
Fire load	0.011 MJ
Weight	1.381 g

## Commercial data

Packaging type	bag
Country of origin	DE
GTIN	4055143690997
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

## Downloads

### Documentation

#### Bid Text

2002-434	Oct 25, 2017	DOC 24.6 kB	Download
----------	--------------	----------------	----------

## smartDATA

### CAD data

3D Download 2002-434	URL	Download
----------------------	-----	----------



## Product family

### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.