

Data sheet | Item number: 2020-106/133-000

1-conductor female plug; Strain relief plate; 1.5 mm<sup>2</sup>; 6-pole

[www.wago.com/2020-106/133-000](http://www.wago.com/2020-106/133-000)



RoHS  Compliant

[BOMcheck.net](https://www.bomcheck.net)

Color: ■

### Item description

According to EN 61984, pluggable connectors without current interrupting capacity shall not be mated and unmated when live or under load.

### Data

#### Electrical data



### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	500 V
Rated impulse voltage (III / 3)	6 kV
Rated current	13.5 A
Legend (ratings)	(III / 3) $\hat{=}$ Overvoltage category III / Pollution degree 3

### Approvals per UL 1059

Rated voltage UL (Use Group B)	300 V
Rated current UL (Use Group B)	15 A
Rated voltage UL (Use Group C)	300 V
Rated current UL (Use Group C)	15 A
Rated voltage UL (Use Group D)	300 V
Rated current UL (Use Group D)	15 A

### Connection data

Connection technology	Push-in CAGE CLAMP <sup>®</sup>
Actuation type	Operating tool Push-in
Connectable conductor materials	Copper Aluminum
Nominal cross section	1 mm <sup>2</sup>
Solid conductor	0.14 ... 1.5 mm <sup>2</sup> / 24 ... 16 AWG
Solid conductor, push-in termination	0.5 ... 1.5 mm <sup>2</sup> / 20 ... 16 AWG
Fine-stranded conductor	0.14 ... 1.5 mm <sup>2</sup> / 24 ... 16 AWG
Fine-stranded conductor with ferrule, push-in termination, from	0.5 mm <sup>2</sup> / 20 AWG
Strip length	9 ... 11 mm / 0.35 ... 0.43 Inch
No. of poles	6
Total number of connection points	6
Total number of potentials	6
Type of wiring	Front-entry wiring

### Geometrical Data

Width	21.7 mm / 0.854 inch
Height	59 mm / 2.323 inch
Depth	22.4 mm / 0.882 inch

### Mechanical data

Marking level	Side marking
---------------	--------------

## Plug connection

Contact type (pluggable connector)	Female connector/socket
Connector connection type	for conductors

## Material Data


Color	gray
Insulating material	Polyamide 66 (PA 66)
Fire load	0.255 MJ
Weight	14.065 g

## Commercial data

Country of origin	DE
GTIN	4050821092285
Customs Tariff No.	85366990990
Product Group	18 (X-COM-System)

## Approvals / Certificates

### Country specific Approvals




Logo	Approval	Certificate name
	CSA DEKRA Certification B.V.	2516073

### UL-Approvals

Logo	Approval	Certificate name
	UL Underwriters Laboratories Inc.	E45172

## Compatible products


### tools

	Item no.: 210-647 Operating tool with partially insulated shaft; Blade (2.5 x 0.4) mm; short	<a href="http://www.wago.com/210-647">www.wago.com/210-647</a>
	Item no.: 210-648 Operating tool with partially insulated shaft; Blade (2.5 x 0.4) mm; short; angled	<a href="http://www.wago.com/210-648">www.wago.com/210-648</a>
	Item no.: 210-719 Operating tool with partially insulated shaft; Type 1, blade (2.5 x 0.4) mm	<a href="http://www.wago.com/210-719">www.wago.com/210-719</a>

## Protective Warning Marker

**Item no.: 2000-115**

Protective warning marker; with high-voltage symbol, black; for 5 terminal blocks

[www.wago.com/2000-115](http://www.wago.com/2000-115)**Marking accessories**



**Item no.: 2009-110**  
Marking strips; on reel; not stretchable; plain; snap-on type

[www.wago.com/2009-110](http://www.wago.com/2009-110)


**Item no.: 2009-113**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113](http://www.wago.com/2009-113)


**Item no.: 2009-113/000-002**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-002](http://www.wago.com/2009-113/000-002)


**Item no.: 2009-113/000-005**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-005](http://www.wago.com/2009-113/000-005)


**Item no.: 2009-113/000-006**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-006](http://www.wago.com/2009-113/000-006)


**Item no.: 2009-113/000-007**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-007](http://www.wago.com/2009-113/000-007)


**Item no.: 2009-113/000-012**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-012](http://www.wago.com/2009-113/000-012)



**Item no.: 2009-113/000-017**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-017](http://www.wago.com/2009-113/000-017)


**Item no.: 2009-113/000-023**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-023](http://www.wago.com/2009-113/000-023)


**Item no.: 2009-113/000-024**  
WMB-Inline; for smartPRINTER; on reel; plain; snap-on type

[www.wago.com/2009-113/000-024](http://www.wago.com/2009-113/000-024)


**Item no.: 210-831**  
Marking strips; on reel; 2.3 mm wide; plain; Self-adhesive

[www.wago.com/210-831](http://www.wago.com/210-831)


**Item no.: 210-832**  
Marking strips; on reel; 3 mm wide; plain; Self-adhesive

[www.wago.com/210-832](http://www.wago.com/210-832)


**Item no.: 210-833**  
Marking strips; on reel; 6 mm wide; plain; Self-adhesive

[www.wago.com/210-833](http://www.wago.com/210-833)


**Item no.: 210-834**  
Marking strips; on reel; 5 mm wide; plain; Self-adhesive




[www.wago.com/210-834](http://www.wago.com/210-834)


**Item no.: 793-3501**  
WMB marking card; as card; plain; snap-on type

[www.wago.com/793-3501](http://www.wago.com/793-3501)



ferrule

	<b>Item no.: 216-241</b> Ferrule; Sleeve for 0.5 mm <sup>2</sup> / AWG 22; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	<a href="http://www.wago.com/216-241">www.wago.com/216-241</a>
	<b>Item no.: 216-242</b> Ferrule; Sleeve for 0.75 mm <sup>2</sup> / AWG 20; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	<a href="http://www.wago.com/216-242">www.wago.com/216-242</a>
	<b>Item no.: 216-243</b> Ferrule; Sleeve for 1 mm <sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90	<a href="http://www.wago.com/216-243">www.wago.com/216-243</a>

Downloads

Documentation

Bid Text

2020-106/133-000	Aug 13, 2018	DOCX 15.6 kB	Download
------------------	--------------	-----------------	----------

smartDATA

CAD data

3D Download 2020-106/133-000	URL	Download
------------------------------	-----	----------

Product family

X-COM S-Mini  
[Show all products from the family](#)

Subject to changes.