



RoHS  
Compliant ✓

BOMcheck.net

Color: ■

## Data

### Electrical data

Rated current (Ex e II)	20 A
-------------------------	------

### Ratings per IEC/EN 60664-1

Rated voltage (III / 3)	800 V
-------------------------	-------

Rated current	25 A
---------------	------

### Geometrical Data

Width	39.9 mm / 1.571 inch
-------	----------------------

Height	19 mm / 0.748 inch
--------	--------------------

Depth	4.1 mm / 0.161 inch
-------	---------------------



## Material Data

Color	light gray
Fire load	0.028 MJ
Weight	5.13 g

## Commercial data

Packaging type	bag
Country of origin	DE
GTIN	4055143690300
Customs Tariff No.	85366990990
Product Group	22 (TOPJOB S)

## Downloads

### Documentation

#### Bid Text

2002-408	Oct 25, 2017	DOC 24.1 kB	Download
----------	--------------	----------------	----------

## smartDATA

### CAD data

3D Download 2002-408	URL	Download
----------------------	-----	----------

## Product family

### TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Learn more about the product family.](#)

[Show all products from the family](#)

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG  
Hansastr. 27  
32423 Minden  
Phone: +49571 887-0 | Fax: +49571 887-169  
Email: [info.de@wago.com](mailto:info.de@wago.com) | Web: [www.wago.com](http://www.wago.com)

Do you have any questions about our products?  
We are always happy to take your call at +49 (571) 887-44222.