

Data

Connection data

No. of poles	4
Connectable sheathed cable diameter	5 ... 9 mm
Abmantellänge	55 mm

Geometrical Data

Width	44.6 mm / 1.756 inch
Height	17 mm / 0.669 inch
Depth	50 mm / 1.969 inch

Mechanical data

Degree of protection	IP20
----------------------	------

Material Data

Color	black
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0

Fire load	0.336 MJ
Weight	12.94 g

Environmental Requirements

Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

Commercial data


Country of origin	DE
GTIN	4045454341756
Customs Tariff No.	85389099990

Approvals / Certificates

Ship Approvals


Logo	Approval	Certificate name
	LR Lloyds Register	02/20050 (E6)

UL-Approvals

Logo	Approval	Certificate name
	cURus Underwriters Laboratories Inc.	E45171 Sec. 9

Compatible products

Marking accessories

	Item no.: 210-333 Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive	www.wago.com/210-333
--	---	--

Downloads

Documentation

Bid Text

770-504/023-000 WINSTA MIDI 4-polig	Feb 8, 2016	DOC 24.1 kB	Download
--	-------------	----------------	----------



smartDATA

CAD data

3D Download 770-504/023-000

URL

Download

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.