

Data

Connection data

No. of poles	3
Connectable sheathed cable diameter	9 ... 13 mm
Abmantelllänge	71 mm

Geometrical Data

Width	34.6 mm / 1.362 inch
Height	15 mm / 0.591 inch
Depth	50 mm / 1.969 inch

Mechanical data

Degree of protection	IP20
----------------------	------

Material Data

Color	white
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0

Weight	15.53 g
--------	---------

Environmental Requirements


Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

Commercial data


Country of origin	DE
GTIN	4045454026226
Customs Tariff No.	85389099990

Approvals / Certificates

Ship Approvals

Logo	Approval	Certificate name
	LR Lloyds Register	02/20050 (E6)

UL-Approvals

Logo	Approval	Certificate name
	cURus Underwriters Laboratories Inc.	E45171 Sec. 9

Compatible products

Marking accessories



Item no.: 210-333

Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive

www.wago.com/210-333

Downloads

Documentation

Bid Text

770-513/021-000	Feb 1, 2016	DOC	Download
WINSTA MIDI 3-polig		24.6 kB	

smartDATA

CAD data



3D Download 770-513/021-000

URL

Download

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.