

Data

Connection data

No. of poles	3
Connectable sheathed cable diameter	4.5 ... 8 mm
Abmantelllänge	55 mm

Geometrical Data

Width	34.6 mm / 1.362 inch
Height	15.2 mm / 0.598 inch
Depth	50 mm / 1.969 inch

Mechanical data

Degree of protection	IP20
----------------------	------

Material Data

Color	white
Insulating material	Polyamide 66 (PA 66)
Flammability class per UL94	V0

Fire load	0.272 MJ
Weight	10.34 g

Environmental Requirements


Surrounding air (operating) temperature	-35 ... 85 °C
---	---------------

Commercial data


Country of origin	DE
GTIN	4044918057523
Customs Tariff No.	85369010000
Product Group	20 (WINSTA)

Approvals / Certificates

Ship Approvals


Logo	Approval	Certificate name
	DNV GL Det Norske Veritas, Germanischer Lloyd	TAE00001Z6

UL-Approvals

Logo	Approval	Certificate name
	cURus Underwriters Laboratories Inc.	E45171 Sec. 9

Compatible products

Marking accessories

	Item no.: 210-333 Marking strips; as a DIN A4 sheet; Strip width 6 mm; Strip length 182 mm; plain; Self-adhesive	www.wago.com/210-333
--	--	--

shield connection

	Item no.: 770-523 Shield connecting plate; for 3-pole plugs and sockets	www.wago.com/770-523
--	---	--

Downloads

Documentation

Bid Text

770-513/023-000

Feb 1, 2016

DOC

Download



WINSTA MIDI 3-polig

24.1 kB

smartDATA

CAD data

3D Download 770-513/023-000

URL

Download

Subject to changes.

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.