



Data

Electrical data

Ratings per IEC/EN 60664-1

Legend (ratings)

(III / 3) ≙ Overvoltage category III / Pollution degree 3

Geometrical Data

Width	190 mm / 7.48 inch
Height	204.36 mm / 8.046 inch

Mechanical data

Degree of protection	IP20
----------------------	------

Material Data

Flammability class per UL94	V0
Weight	290 g



## Environmental Requirements

Surrounding air (operating) temperature -35 ... 85 °C

---

## Commercial data

Country of origin	DE
GTIN	4050821313144
Customs Tariff No.	73269098900
Product Group	20 (WINSTA)

---

## Downloads

### Documentation

#### Bid Text

770-680	Jan 29, 2016	DOC	Download
WINSTABOXEN		22.0 kB	

---

Subject to changes.