



TYPE	A	B	C	R
TRH 1212	99.0±0.5	110.0±1.0	4.5	2.25
TRH 1216	135.0±0.5	146.0±1.0	4.5	2.25
TRH 1220	175.0±0.5	186.0±1.0	4.5	2.25
TRH 1520	159.0±0.5	170.0±1.0	4.5	2.25
TRH 24	215.0±0.5	226.0±1.0	4.5	2.25
TRH 2330	274.5±0.5	285.5±1.0	4.5	2.25
TRH 2036	329.0±0.5	340.0±1.0	6.0	3.0
ARH 12	94.0±0.5	105.0±1.0	7.0	3.5
ARH 16	129.0±0.5	140.0±1.0	7.0	3.5
ARH 22	192.0±0.5	203.0±1.0	7.0	3.5
ARH 26	229.0±0.5	240.0±1.0	7.0	3.5
ARH 36	332.0±0.5	343.0±1.0	7.0	3.5
ARH 40	372.0±0.5	383.0±1.0	7.0	3.5
ARH 60	569.0±0.5	580.0±1.0	7.0	3.5
ARH 1636	329.0±0.5	340.0±1.0	7.0	3.5
ARH 1656	529.0±0.5	540.0±1.0	7.0	3.5
ARH 2320	169.0±0.5	180.0±1.0	7.0	3.5
ARH 2328	249.0±0.5	260.0±1.0	7.0	3.5
ARH 2333	299.0±0.5	310.0±1.0	7.0	3.5
PRH 2526	227.0±0.5	238.0±1.0	7.0	3.5