


Cermet preset potentiometers

Typ TGN 825 M

Basic design: width 9 mm





Technical data Resistance value and $100 \Omega - 1 M\Omega \pm 20 \%$ Stopper strength 1.0 K gf-cm tolerance **Taper** lin **Operation life** 100 cycle resistance value ± 10 % Power rating 0.5 W / 70 °C **Temperature characteristics** 3 % @ 70 °C 5HR Max. working voltage 250 V Temperature coefficient + 150 ppm / °C Residual resistance 10 Ω @ R \pm 1 K Ω , 1%@ R 1 Resistance to soldering heat 260 °C 5 sec. Mech. rotation angle 260 ± 20 ° Working temperature - 40 °C - + 125°C