

## Ferrule - AI-TWIN 2X 1,5 -10 BK - 3201534

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 18 mm, Color: black

### Key commercial data

package_quantity	100
GTIN	4017918106591

### Technical data

#### Dimensions

Length (b)	18 mm
Sleeve length	10 mm
Inner dimension of the insulating collar (d)	3.6 mm
Ferrule diameter	2.3 mm
Insulating collar thickness	0.3 mm
Sleeve wall thickness	0.15 mm

#### Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C

#### General

Color	black
Components	free from silicone and halogen
Inflammability class according to UL 94	HB
Material	E-CU

### classifications

#### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201

## Ferrule - Al-TWIN 2X 1,5 -10 BK - 3201534

### classifications

#### eCl@ss

eCl@ss 8.0	27400201
------------	----------

#### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>