

Ferrule - A 1 - 8 - 3202517

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Ferrule, Length: 8 mm, Color: silver

The figure shows variant A 1-6

Product Features

- ✓ The A 0,25.. ferrules can also be used to process 0.14 mm² conductors
- ✓ The dimensions of the ferrules conform to DIN 46228-1
- ✓ The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

Key commercial data

package_quantity	1000
GTIN	4017918157210

Technical data

Dimensions

Length (b)	8 mm
Sleeve length	7.3 mm
Inner dimension of the insulating collar (d)	2.5 mm
Ferrule diameter	1.4 mm
Sleeve wall thickness	0.15 mm

Ambient conditions

Max. permanent temperature	105 °C
----------------------------	--------

General

Color	silver
-------	--------

classifications

eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201

Ferrule - A 1 - 8 - 3202517

classifications

eCl@ss

eCl@ss 8.0	27400201
------------	----------

ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005

UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

approvals

CSA / CSAus / cCSAus /

Approval details

CSA 	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	

CSAus	
Nominal voltage UN	
Nominal current IN	
mm²/AWG/kcmil	

cCSAus

Drawings