

Conductor marking collar - PMH 1:UNBEDRUCKT - 0800459

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Conductor marking collar, yellow, Unlabeled, Mounting type: Thread on, Cable diameter: 1.9-3.8 mm

The illustration shows a combination of upper case letters, symbols and figures in versions PMH -0, -2 and -4

Key commercial data

package_quantity	100
GTIN	4017918006013

Technical data

Ambient conditions

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-45 °C ... 70 °C
Ambient temperature (assembly)	> 10 °C

General

Color	yellow
Components	Free from silicone, halogen and cadmium
Inflammability class according to UL 94	V0
Material	EVA

classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27400401
eCl@ss 7.0	27400401
eCl@ss 8.0	27400401

ETIM

ETIM 2.0	EC000761
-----------------	----------

Conductor marking collar - PMH 1:UNBEDRUCKT - 0800459

classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC001530
ETIM 5.0	EC001530

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

accessories

Mounting material

AFD-2 - 0800679



AFD-1,5 - 0800789



Assortment box

SORTI 4/12 - 5020658



Drawings