

# Conductor marking collar - PMH 2:UNBEDRUCKT - 0800491

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Conductor marking collar, yellow, Unlabeled, Mounting type: Thread on, Cable diameter: 3-6 mm

The illustration shows a combination of upper case letters, symbols and figures in versions PMH -0, -2 and -4

## Key commercial data

<b>package_quantity</b>	100
<b>GTIN</b>	4017918006051

## Technical data

### Ambient conditions

<b>Wipe resistance</b>	DIN EN 61010-1 (VDE 0411-1)
<b>Ambient temperature (operation)</b>	-45 °C ... 70 °C
<b>Ambient temperature (assembly)</b>	> 10 °C

### General

<b>Color</b>	yellow
<b>Components</b>	Free from silicone, halogen and cadmium
<b>Inflammability class according to UL 94</b>	V0
<b>Material</b>	EVA

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	24190219
<b>eCl@ss 4.1</b>	24190219
<b>eCl@ss 5.0</b>	27149103
<b>eCl@ss 5.1</b>	27141137
<b>eCl@ss 6.0</b>	27400401
<b>eCl@ss 7.0</b>	27400401
<b>eCl@ss 8.0</b>	27400401

### ETIM

<b>ETIM 2.0</b>	EC000761
-----------------	----------

# Conductor marking collar - PMH 2:UNBEDRUCKT - 0800491

## classifications

### ETIM

<b>ETIM 3.0</b>	EC000761
<b>ETIM 4.0</b>	EC001530
<b>ETIM 5.0</b>	EC001530

### UNSPSC

<b>UNSPSC 6.01</b>	30211811
<b>UNSPSC 7.0901</b>	39121410
<b>UNSPSC 11</b>	39121410
<b>UNSPSC 12.01</b>	39121410
<b>UNSPSC 13.2</b>	39121410

## accessories

### Mounting material

AFD-3 - 0800682



AFD-2 - 0800679



### Assortment box

SORTI 4/12 - 5020658



## Drawings