

## ASSMANN USB 2.0 connection cable

AK-300101-050-S  
EAN 4016032282617



### USB 2.0 connection cable, type A M/M, 5.0m, USB 2.0 conform, bl

For connection of external USB devices (with A socket) to the USB Host (e. g. PC, Notebook or USB Hub). Datatransferrate up to 480 Mbps (High-Speed).

**Allows a reliable and fast connection of external USB devices with the PC, also about longer distances.**

- Connector 1: USB A, plug
- Connector 2: USB A, plug
- USB compliance: USB 2.0

- Hoods: molded
- Shielding: Double shielding
- AWG: 28
- Wire material: CU
- Connector surface: nickel-plated
- Ferrite filter: none
- Color cable: black
- Color connector: black
- Length: 5 m
- Assortment: USB Cables

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm <sup>3</sup>
Packaging Unit Carton	50	9.90	38.00	30.00	22.00	25,080.00
Packaging Unit Inside	5	0.99	2.00	16.00	18.00	576.00
Packaging Unit Single	1	0.20	2.00	16.00	18.00	576.00
Net single without Packaging	1	0.00	2.00	13.00	14.00	364.00

### More images:

