

1		2		3		4		5		6		7							
A		RoHS & REACH Compliant CN 1:HDMI AM,INS:BLACK CN 2:HDMI AM,INS:BLACK										Signature		Revision History		Date		Rev.	
												Achy		For Bulk Production		JUL,08,2016		00	
												Achy		Optimization of drawing		May,10,2017		01	
B												B							
C												C							
D												D							
E		NOTES: 1.Cable:(1/0.254BC*1P+1/0.254CCS+AL/M)*5C+1/0.254BC*4C+AL+1/0.254BC+B(64/0.12ALM), Jacket:PVC/Black,OD:6.0±0.2mm.Cable printing:High Speed HDMI Cable with Ethernet 2.Connector:CN1&CN2:HDMI A/M,Black Insulator,Shell:Gold plated,Contact:Gold plated 3.Inner moulded:LDPE. 4.Hood:Moulded type,PVC 88A,Color:Black. 5.Dust cap:For HDMI A type male,LDPE. 6.TEST:(1)100% OPEN SHORT & MISS WIRE TEST. (2)CONDUCTOR RESISTANCE 3 ohm Max. (3)INSULATION RESISTANCE:DC 300V 10MΩ Min (4)HD-TV:1080P,60HZ.										E							
F												F							
G		Cross Section:										G							
H		ASSMANN Electronic GmbH										H							
1		2		3		4		5		6		7							

Date		Name		Part No.	
May.10,2017		Achy		AK-330107-010-S	
May.10,2017		Helen		EAN:4016032290940	
15May, 2017		Joe			
Title				HDMI High Speed connection cable,type A M/M,1.0m,w/Ethernrt,Ultra HD 60p, bl,gold	
Scale		N/A		Sheet	
Unit		MM		1/2	

	1	2	3	4	5	6	7																
A	RoHS & REACH Compliant					<table border="1"> <tr> <th>Signature</th> <th>Revision History</th> <th>Date</th> <th>Rev.</th> </tr> <tr> <td>Achy</td> <td>For Bulk Productio</td> <td>JUL,08,2016</td> <td>00</td> </tr> <tr> <td>Achy</td> <td>Optimization of drawing</td> <td>May,10,2017</td> <td>01</td> </tr> </table>		Signature	Revision History	Date	Rev.	Achy	For Bulk Productio	JUL,08,2016	00	Achy	Optimization of drawing	May,10,2017	01				
Signature	Revision History	Date	Rev.																				
Achy	For Bulk Productio	JUL,08,2016	00																				
Achy	Optimization of drawing	May,10,2017	01																				
B	Package Details Single Cable <table border="1"> <thead> <tr> <th>P/N</th> <th>Cable Length</th> <th>Rolling Size (Single Cable)</th> <th>Polybag Type (Single Cable)</th> <th>Bag Size (Single Cable)</th> <th>Article Weight (Single Cable)</th> </tr> </thead> <tbody> <tr> <td>AK-330107-010-S</td> <td>1.0m</td> <td>110±10mm</td> <td>Ordinary Polybag (Heat Sealed)</td> <td>230*180*0.05mm</td> <td>0.056kg</td> </tr> </tbody> </table>					P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)	AK-330107-010-S	1.0m	110±10mm	Ordinary Polybag (Heat Sealed)	230*180*0.05mm	0.056kg	Single Cable					
P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)																		
AK-330107-010-S	1.0m	110±10mm	Ordinary Polybag (Heat Sealed)	230*180*0.05mm	0.056kg																		
C	Inner Packing Unit <table border="1"> <thead> <tr> <th>P/N</th> <th>Cable Length</th> <th>Quantity (Inner Packing Unit)</th> <th>Type (Inner Packing Unit)</th> <th>Size (Inner Packing Unit)</th> <th>Weight (Inner Packing Unit)</th> </tr> </thead> <tbody> <tr> <td>AK-330107-010-S</td> <td>1.0m</td> <td>10 pcs</td> <td>Polybag (Heat Sealed)</td> <td>490*330*0.04mm</td> <td>0.568kg</td> </tr> </tbody> </table>					P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)	AK-330107-010-S	1.0m	10 pcs	Polybag (Heat Sealed)	490*330*0.04mm	0.568kg						
P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)																		
AK-330107-010-S	1.0m	10 pcs	Polybag (Heat Sealed)	490*330*0.04mm	0.568kg																		
D	Carton Details <table border="1"> <thead> <tr> <th>P/N</th> <th>Cable Length</th> <th>Quantity (Carton)</th> <th>Measurement (Carton)</th> <th>N.W. (Carton)</th> <th>G.W. (Carton)</th> </tr> </thead> <tbody> <tr> <td>AK-330107-010-S</td> <td>1.0m</td> <td>100 pcs</td> <td>35x28x25cm</td> <td>5.8kg</td> <td>6.3kg</td> </tr> </tbody> </table>					P/N	Cable Length	Quantity (Carton)	Measurement (Carton)	N.W. (Carton)	G.W. (Carton)	AK-330107-010-S	1.0m	100 pcs	35x28x25cm	5.8kg	6.3kg	Inner Packing Unit					
P/N	Cable Length	Quantity (Carton)	Measurement (Carton)	N.W. (Carton)	G.W. (Carton)																		
AK-330107-010-S	1.0m	100 pcs	35x28x25cm	5.8kg	6.3kg																		
E																							
F																							
G						<table border="1"> <thead> <tr> <th></th> <th>Date</th> <th>Name</th> <th>Part No.</th> </tr> </thead> <tbody> <tr> <td>Drawn by</td> <td>May.10,2017</td> <td>Achy</td> <td>AK-330107-010-S</td> </tr> <tr> <td>Checked by</td> <td>May.10,2017</td> <td>Helen</td> <td>EAN:4016032290940</td> </tr> <tr> <td>Approved by</td> <td>15May, 2017</td> <td>Joe</td> <td></td> </tr> </tbody> </table>			Date	Name	Part No.	Drawn by	May.10,2017	Achy	AK-330107-010-S	Checked by	May.10,2017	Helen	EAN:4016032290940	Approved by	15May, 2017	Joe	
	Date	Name	Part No.																				
Drawn by	May.10,2017	Achy	AK-330107-010-S																				
Checked by	May.10,2017	Helen	EAN:4016032290940																				
Approved by	15May, 2017	Joe																					
H	★ "ROTTERDAM" is for Sea Freight shipment ★ "COLOGNE" is for Air Freight shipment ★ "LUDENSCHIED" is for Fedex or UPS shipment					ASSMANN Electronic GmbH <table border="1"> <thead> <tr> <th>Title</th> <th>Scale</th> <th>N/A</th> <th>Sheet</th> </tr> </thead> <tbody> <tr> <td>HDMI High Speed connection cable,type A M/M,1.0m,w/Ethernrt,Ultra HD 60p, bl,gold</td> <td>Unit</td> <td>MM</td> <td>1/2</td> </tr> </tbody> </table>		Title	Scale	N/A	Sheet	HDMI High Speed connection cable,type A M/M,1.0m,w/Ethernrt,Ultra HD 60p, bl,gold	Unit	MM	1/2								
Title	Scale	N/A	Sheet																				
HDMI High Speed connection cable,type A M/M,1.0m,w/Ethernrt,Ultra HD 60p, bl,gold	Unit	MM	1/2																				