

Rating	16A 12VDC
Contact Resistance	50m ohm Max.
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-20℃~85℃
Circuit	3P SPST ON-OFF

Mounting Hole




Thickness	X	Y
0.75...1.25	19.2-0.1	13+0.1
1.25...2	19.4-0.1	13+0.1
2...3	19.8-0.1	13+0.1

Circuit Diagram



Material:
Frame: Black, Nylon 66 (94-V2)
Lens: Red Clear, PC
Terminals: Silver plated, Copper alloy
Lamp: LED(Red)
Hot stamping: None



參1821701
CEI

△	Date	Name	Descriptions

Drawn	Checked	Approved	SCI No.		Model Name	ROCKER SWITCH	
黃 平 平			Customer No.		Model No.	R13-66B-02	REV.
07/18/'08			Unit	mm			0