

DATA SHEET

Model MS-500-H-MP (Red)
 Toggle Switch

Specification

- Rating : 6A 125VAC
- Circuit: DPDT ON-OFF-ON
- Contact Resistance : 20mΩ or less
- Insulation Resistance :
 1000V DC Megger 100MΩ or more
- Voltage Breakdown :
 1000V AC (Between Terminals)
- Durability : Rated Load with Resistance
 5,000 cycles
 Non-Load : 30,000 cycles

Construction

- 1) Lever Brass Nickel Plated
- 2) Metal Brass Nickel Plated
- 3) Hex Nut Steel Nickel Plated
- 4) Lock Washer Steel Unichromate
- 5) Lock Ring Steel Unichromate
- 6) Frame Stainless Steel Cleaning
- 7) Body Melamine Phenolic Resin (Blue)
- 8) Terminal Silver-clad Copper Silver Plate
- 9) Common Terminal Copper Silver Plated
- 10) Rx. Lever ABS (RED)

