




Rating	20A 12V DC	<b>Mounting Hole</b> 	<b>Circuit Diagram</b> 
Contact Resistance	50m ohm Max		
Insulation Resistance	DC 500V 100M ohm		
Dielectric Strength	AC 1500V 1minute		
Switch Function	3P SPST ON-OFF		



CEI

Date		Name		Description			NO	
Drawn	Checked	Approved	SCI BOM No.	1810216	Model Name	Toggle Switch		
黄平平	杨金江		Customer No.		Model No.	R13-61L	REV.	
07/09/'08	07/09/08"		Unit	mm	SHIN CHIN INDUSTRIAL CO., LTD.			0