

R13-61 -



20A 12V DC

Ø 12.2

± 2 mm max



0 1 .250" SQ

LEVER



A,B, C,D
L Transparent Lever



L 2 Metal Lever



L 3 Metal Lever



L 4 Transparent Lever



L 5 Transparent Lever

