

Components of electronic housing - BC 107,6 OT U11 KMGY - 2896076

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Upper part for installation housing BC, width: 107.6 mm, wiring space depth: 11 mm

The illustration shows the gray version

Key commercial data

package_quantity	10
GTIN	4046356096492

Technical data

General

Housing type	Component housing
Housing material	polycarbonate
Color	light gray

Dimensions

Length	89.7 mm
Constructional height	62.2 mm
Width	107.6 mm

Technical data

Inflammability class according to UL 94	V0
--	----

classifications

eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

ETIM

Components of electronic housing - BC 107,6 OT U11 KMGY - 2896076

classifications

ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC000886




UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

approvals

UL Recognized / GOST / GOST /


Approval details



Drawings

Components of electronic housing - BC 107,6 OT U11 KMGY - 2896076

Dimensioned drawing



The dimensional drawing shows the item along with the lower part of the housing (terminal installation depth 11.1 mm) and the housing cover

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>