

## AQUILINE FOOT SWITCH

EN 60529 Degree of Protection IP20

- Maximum versatility, total performance.
- SPDT, DPDT, or Two-Stage Operation.
- Rustproof and corrosionproof reinforced polymeric material for rugged duty.
- Two stage model has cast zinc cover and formed steel base.
- 971-SWNO210 & 971-SWNO210A are NEMA Type 1, 4X, 6 & 6P – UL Enclosure 1, 4X, 6 & 6P, and IP68
- Non-skid base pad.
- Raised ribs on treadle for positive traction during operation.
- Attractive non-glare finish. Custom colors, and color matching available with quantity orders.
- Integrated adjustable strain relief clamp accommodates cord sizes from .250 Dia. to .400 Dia.
- Patented
- Full and twin guards (#522-B14 and #522-B12) as well as accessory base units available for configurations using multiple switches.
- **Stainless steel full guard (single) #522-K26 available.**

Size: 4" x 3<sup>3</sup>/<sub>16</sub>" x 1<sup>1</sup>/<sub>32</sub>"

Weight: Approx. 3.6 oz.; Metal Aquiline .9 lbs or .410 kg.



## AC VARIABLE SPEED CONTROL FOOT SWITCH

EN 60529 Degree of Protection IP20

- Variable control of small fractional horsepower Universal AC/DC motors only, leaving hands free.
- Half wave in the variable speed mode, full wave at full speed.
- Optional SPDT auxiliary off/on switch.
- Supplied with dual cordsets, single series plug or custom modified for the O.E.M.
- Polymeric material will not rust or corrode.
- Standard color is black; custom colors may be quoted on large O.E.M. orders.

Size: 6<sup>3</sup>/<sub>4</sub>" x 4" x 2<sup>1</sup>/<sub>4</sub>"














Weight: 1 lb. 3 oz.



**⚠ WARNING SEE INSIDE FRONT COVER**



### SPECIFICATIONS

(Special variations are available to the O.E.M. on special order on the models listed below)

APPROVALS	CATALOG NO.	DESCRIPTION	COLOR <sup>†</sup>	CIRCUIT	ELECTRICAL RATINGS
 CE	971-S	Momentary	Dark Gray	SPDT	
 CE	971-SA	Momentary	Light Gray	SPDT	
 CE	971-SB	Momentary	Blue	SPDT	15 A 125-250 VAC
 CE	971-SM*	Momentary	Black	SPDT	½ H.P. 125-250 VAC
 CE	971-SO	Momentary	Orange	SPDT	
 CE	971-SY	Momentary	Yellow	SPDT	
 CE	971-SC26Ⓢ	Momentary	Dark Gray	SPDT WIRED N.O.	10 A 125-250 VAC
 CE	971-SC26AⓈ	Momentary	Light Gray	SPDT WIRED N.O.	½ H.P. 125-250 VAC
 CE	971-SWNO210**	Momentary	Dark Gray	SPST WIRED N.O.	3 A 25 VAC
 CE	971-SWNO210A**	Momentary	Light Gray	SPST WIRED N.O.	
 CE	972-S*	Two-stage Momentary	Black	SPDT EACH STAGE	15 A 125-250 VAC
 CE	974-S	Momentary	Dark Gray	DPDT	½ H.P. 125-250 VAC
 CE	974-SA	Momentary	Light Gray	DPDT	

\*Die cast metal housing. \*\*Meets IP68 & is supplied with 10ft. 18/2 cord without plug. Ⓢ Supplied with 6ft. 18/2 cord without plug.

†Cover only with black base

	AC VARIABLE SPEED CONTROL CATALOG NUMBER	DESCRIPTION	ELECTRICAL RATINGS	CORDSETS
	980-SC3	Momentary	6 A 125 VAC	6' 18/3 SVT with 3-prong plug 1' 18/3 SVT with mating receptacle
	981-SC36	Momentary	4 A 250 VAC	6' 18/3 SVT with outer jacket stripped back 1' 18/3 SVT with outer jacket stripped back