



MICRO SWITCH

FREEPORT, ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ-2RQ1-A2

ALF4500

BZ-2RQ1-A2
PAGE 1 OF 1
REPLACES

M
DRAWING NUMBER
9

ISSUE

REVISIONS

A	CO17410	G C H	22 MAY 63
B	CO-73287-4	D H D	17 MAY 93
C	CO-77589	K D R	29 MAR 94
D	CO-82133		
E	CO93346		
F	0015139	DLT	10 SEP 98
		TSG	23 AUG 05

RELEASE NO. 15 JUN 63

CHECK 23 AUG 05

CHECK 29 MAR 94

CHECK 10 SEP 98

CHECK 23 AUG 05

FORMTEK
FO-50376
DRAWN
G C H
22 MAY 63



- NOTES**
- ① MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS
 - ② HARDWARE FURNISHED UNASSEMBLED

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 9 - 13 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	-L96- 15 A - 125, 250, OR 480 VAC 1/2 A - 125 VDC, 1/4 A - 250 VDC 1/8 HP - 125 VAC, 1/4 HP - 250 VAC CE EN05 EC RU 16A 250V ~ T85 5E4	UNLESS OTHERWISE NOTED
DIFFERENTIAL TRAVEL ----- 0004 - .0020		DIMENSIONS ARE IN INCHES
OVERTRAVEL ----- .219 MIN		TOLERANCES ARE:
		ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
		WEIGHT .094 LB