

DATA SHEET

B/N 703036
MS-500 C-BC Toggle Switch

Specifications :

Rating : 6A.125V. AC
 Circuit : ON-OFF-ON SPDT (3 Pin)
 Contact Resistance : 20mΩ or less, initial characteristics
 Insulation Resistance : DC500V Megger. 100MΩ or more
 Dielectric Strength : 1000V, AC (Between terminals) 1500V, AC (Between Live metal parts and dead metal parts) 50/60Hz for 1minute
 Durability : Rated load with Resistance, 5,000 cycles Non-load, 30,000 cycles

Construction :

	Materials	Finish
① Cap	Vinyl Chloride	Black
② Lever	Brass	Chrome Plated
③ Metal	Brass	Nickel Plated
④ Hex Nut	Steel	Nickel Plated
⑤ Lock Washer	Steel	Unichromate
⑥ Locking Ring	Steel	Unichromate
⑦ Frame	Stainless Steel	Cleaning
⑧ Body	Melamine Phenolic	Blue
⑨ Terminal	Silver Clad Copper	Silver Plated
⑩ Common Terminal	Copper	Silver Plated

Unit : mm

