


















# SHAFT DETAILS

When specifying fixing options below, indicate shaft size and type, i.e: screw fix (SF), push fix (D), splined (SPL) or collet.

SHAFT SIZE	3mm	4mm	4mm	4mm	6mm	6mm	6mm U.S.A.	6mm	6mm	¼ inch	¼ inch	¼ inch	¼ inch	MARKER DOT & LINE OPTIONS
KNOB TYPE														
K1C					●				●	●		●		S (std)
K4C									∅			●		Z
K5, K8					●				●	●		●		Z, S
K6C, K6C/SKT				●		∅			●			●		D SL N
K7C					●	∅			●	●		●		Z
K85, K88		●			●	●				●	●			Z (std)
K85M		●			●	●	●			●	●			Z (std)
K86R, K86AR					●		●							LZ
K87MA, K87MB +		∅			●	●	●			●				LZ
K9 *	●		●	●	●	●	●	●	●	●		●	●	LDZ
K10 *	●		●	●	●	●	●	●	●	●		●	●	LDZ
K11	●		●	●	●	●	●	●	●	●		●	●	LDZ
K12	●		●	●	●	●	●	●	●	●		●	●	LDZ
K14				●	●		K14P		●	●		●		Z
K15, K15P				●	●				●	●		●		K15 - Z
K16, K16P				●	●		K16P		●	●		●		K16 - Z
K17									∅	∅		●		Z (std)
K18					●				●			●		
K19					●									D
K21				●	●	●			●	●		●		Z D
C18, C18/SKT					●	●	●			●				C18 - Z(std) C18/SKT SL N
KM12B, KM15B					●									
KM20B, KM40B, KM50B					●		∅							
KMK SERIES					●		●							
KMR SERIES					●		∅			KMR40D				
KEY	<b>COLLET</b> 	<b>SPLINED</b> 	<b>D-SPRING</b> 	<b>SCREW</b> 	● = AVAILABLE - STD ∅ = ENQUIRE IF REQD.				L - Body line D - Cap dot S - Skirt dot Z - Cap line SL - Skirt line N - Numbered					

\* For All Black model only - version with integral cap is available. NOT ALL PUSH FIX MODELS HAVE METAL SPRINGS.

+ Including `R` `Soft Touch` versions.