

TERMINAL CALL-OUTS MAY ALSO BE LISTED NUMERICALLY


3 - M4 X 4.9 mm  
TERMINAL SCREW AND  
INTERNAL TOOTHED  
LOCK WASHER

SWITCH CHARACTERISTICS	
ELECTRICAL RATING	20A 250VAC UL APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	650 GMS
RELEASE FORCE MIN.	200 GMS
PRETRAVEL MAX.	.027 [0.7 mm]
OVERTRAVEL MIN.	.005 [0.13 mm]
MOVE. DIFF. MAX.	.008 [0.2 mm]
OPERATING POSITION	.610 TO .641 [15.5 TO 16.3 mm]

NOTES:  
RECOMMENDED MOUNTING:  
M4 FASTENER WITH 6.00 IN-LB [7.00 KGF-CM] OF TORQUE MAX.

REV	ECN NO.	DATE	PREP	APVD
A	12994	20-Jun-05	TLM	SG

DWN: JED/TLM  
APVD: SG  
DATE: 20-Jun-05



THE CONFIDENTIAL AND PROPRIETARY INFORMATION CONTAINED IN THIS DOCUMENT IS OWNED BY CHERRY ELECTRICAL PRODUCTS, A DIVISION OF THE CHERRY CORPORATION WHO MUST GIVE WRITTEN PERMISSION BEFORE THE DOCUMENT OR INFORMATION CAN BE COPIED, DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED		
X.XX	X.XXX	ANGLES
± 0.02	± 0.015	± 5

PROJECT / ESN  
05-0457A



11200 88TH AVENUE  
PLEASANT PRAIRIE, WI 53158

SPEC DRAWING	
B	ITEM NO. GPTBNA01
SCALE: 2:1	SH 1 OF 1