



3 - M4 X 4.9 mm
TERMINAL SCREW AND
INTERNAL TOOTHED
LOCK WASHER

CHARACTERISTICS	
ELECTRICAL RATING	15A 125VAC OR 250VAC UL APPROVED
TERMINAL	SCREW
OPER. FORCE MAX.	350 GMS
RELEASE FORCE MIN.	114 GMS
PRETRAVEL MAX.	.016 [0.4 mm]
OVERTRAVEL MIN.	.216 [5.5 mm]
MOVE. DIFF. MAX.	.002 [0.05 mm]
OPERATING POSITION	.826 TO .890 [21.0 TO 22.6 mm]

DWN: JED
APVD: SB
DATE: 25-May-04
THIRD ANGLE PROJECTION

THE CONFIDENTIAL AND PROPRIETARY INFORMATION CONTAINED IN THIS DOCUMENT IS OWNED BY CHERRY ELECTRICAL PRODUCTS, A DIVISION OF THE CHERRY CORPORATION WHO MUST GIVE WRITTEN PERMISSION BEFORE THE DOCUMENT OR INFORMATION CAN BE COPIED, DISCLOSED OR USED IN ANY WAY.

TOLERANCE UNLESS SPECIFIED

X.XX	X.XXX	ANGLES
± 0.02	± 0.015	± 5

PROJECT / ESR

CHERRY
ELECTRICAL PRODUCTS
3600 SUNSET AVENUE
HAUKEGAN, IL 60087

NAME / DESCRIPTION: SWITCH

B	ITEM NO.	GPTCNH01
SCALE: 2:1		SH OF

REV	ECN NO.	DATE	PREP	APVD
B	11388	02-Jun-04	JED	SB