

# Power module - EMD-SL-PS- 24DC - 2885359

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Power modules, pluggable, for EMD-SL-..., supply voltage: 20 V DC ... 30 V DC

## Product Features

- Separately adjustable startup and response delays
- Variable supply voltage range
- Adjustable via potentiometer on the front

## Key commercial data

<b>package_quantity</b>	1
<b>GTIN</b>	4046356049887

## Technical data

### Dimensions

<b>Width</b>	32 mm
<b>Height</b>	35 mm
<b>Depth</b>	16 mm

### Ambient conditions

<b>Ambient temperature (operation)</b>	-25 °C ... 55 °C
<b>Ambient temperature (storage/transport)</b>	-25 °C ... 70 °C

### Input data

<b>Nominal input voltage</b>	24 V DC
<b>Input voltage range DC</b>	20 V DC ... 30 V DC

## classifications

### eCl@ss

<b>eCl@ss 4.0</b>	27371105
<b>eCl@ss 4.1</b>	27371105
<b>eCl@ss 5.0</b>	27049090
<b>eCl@ss 5.1</b>	27049201
<b>eCl@ss 6.0</b>	27049201
<b>eCl@ss 7.0</b>	27049201
<b>eCl@ss 8.0</b>	27049201

## Power module - EMD-SL-PS- 24DC - 2885359

### classifications

#### ETIM

<b>ETIM 2.0</b>	EC001438
<b>ETIM 3.0</b>	EC001438
<b>ETIM 4.0</b>	EC001438
<b>ETIM 5.0</b>	EC001438

#### UNSPSC

<b>UNSPSC 6.01</b>	30211916
<b>UNSPSC 7.0901</b>	39121535
<b>UNSPSC 11</b>	39121535
<b>UNSPSC 12.01</b>	39121535
<b>UNSPSC 13.2</b>	39121535

### Drawings

© Phoenix Contact 2013 - all rights reserved  
<http://www.phoenixcontact.com>