

Power module - EMD-SL-PS45-230AC - 2885294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Power modules, pluggable, for EMD-FL-..., supply voltage: 195 V AC ... 264 V AC

Product Features

- Variable supply voltage range
- Adjustable asymmetry
- Adjustable via potentiometer on the front
- Adjustable response delay

Key commercial data

package_quantity	1
GTIN	4017918996536

Technical data

Dimensions

Width	32 mm
Height	35 mm
Depth	26 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Ambient temperature (storage/transport)	-25 °C ... 70 °C

Input data

Nominal input voltage	230 V AC (50/60 Hz)
Input voltage range AC	195 V AC ... 264 V AC

classifications

eCl@ss

eCl@ss 4.0	27371105
eCl@ss 4.1	27371105
eCl@ss 5.0	27049090
eCl@ss 5.1	27049201
eCl@ss 6.0	27049201
eCl@ss 7.0	27049201

Power module - EMD-SL-PS45-230AC - 2885294

classifications

eCl@ss

eCl@ss 8.0	27049201
------------	----------

ETIM

ETIM 2.0	EC001438
ETIM 3.0	EC001438
ETIM 4.0	EC001438
ETIM 5.0	EC001438

UNSPSC

UNSPSC 6.01	30211916
UNSPSC 7.0901	39121535
UNSPSC 11	39121535
UNSPSC 12.01	39121535
UNSPSC 13.2	39121535

Drawings

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>